

**CBC-SP 14-120/25 BK****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Similar to illustration**

Spiral and webbing hoses are particularly suitable for the construction of space-saving cable routing systems in switch gears and control cabinets. They are used for guiding, protecting and bundling cables and wires - for example, in the transition between the enclosure interior and the door.

**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | Protective cable hose coil |
| Order No.  | <a href="#">2588500000</a> |
| Type       | CBC-SP 14-120/25 BK        |
| GTIN (EAN) | 4050118602555              |
| Qty.       | 25 m                       |

## CBC-SP 14-120/25 BK

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Dimensions and weights

|          |            |                 |            |
|----------|------------|-----------------|------------|
| Length   | 100,000 mm | Length (inches) | 3.937 inch |
| Diameter | 12 mm      | Net weight      | 32.6 g     |

### Temperatures

|                             |             |                             |        |
|-----------------------------|-------------|-----------------------------|--------|
| Operating temperature range | -15...60 °C | Operating temperature, min. | -15 °C |
| Operating temperature, max. | 60 °C       |                             |        |

### General information

|                             |                 |                       |                        |
|-----------------------------|-----------------|-----------------------|------------------------|
| Bundle diameter, max.       | 120 mm          | Bundle diameter, min. | 14 mm                  |
| Colour                      | black, RAL 7021 | Diameter              | 12 mm                  |
| Material                    | Polyethylene    | Nominal diameter      | 9.6 mm                 |
| Operating temperature range | -15...60 °C     | Usable cross-section  | 11,309 mm <sup>2</sup> |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001182    | ETIM 7.0    | EC001182    |
| ETIM 8.0    | EC001182    | ECLASS 9.1  | 27-43-03-03 |
| ECLASS 10.0 | 27-43-03-03 | ECLASS 11.0 | 27-43-03-03 |
| ECLASS 12.0 | 27-43-03-03 |             |             |

### Approvals

|      |         |
|------|---------|
| ROHS | Conform |
|------|---------|

### Downloads

|            |  |
|------------|--|
| Catalogues | <a href="#">Catalogues in PDF-format</a> |
|------------|--|