

CBC-SP 12-100/25 BK**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Similar to illustration

Spiral and webbing hoses are particularly suitable for the construction of space-saving cable routing systems in switch gears and control cabinets. They are used for guiding, protecting and bundling cables and wires - for example, in the transition between the enclosure interior and the door.

General ordering data

Version	Protective cable hose coil
Order No.	2588520000
Type	CBC-SP 12-100/25 BK
GTIN (EAN)	4050118602548
Qty.	25 m

CBC-SP 12-100/25 BK

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Length	100,000 mm	Length (inches)	3.937 inch
Diameter	10 mm	Net weight	28 g

Temperatures

Operating temperature range	-15...60 °C	Operating temperature, min.	-15 °C
Operating temperature, max.	60 °C		

General information

Bundle diameter, max.	100 mm	Bundle diameter, min.	12 mm
Colour	black, RAL 7021	Diameter	10 mm
Material	Polyethylene	Nominal diameter	7.6 mm
Operating temperature range	-15...60 °C	Usable cross-section	7,853 mm ²

Classifications

ETIM 6.0	EC001182	ETIM 7.0	EC001182
ETIM 8.0	EC001182	ECLASS 9.1	27-43-03-03
ECLASS 10.0	27-43-03-03	ECLASS 11.0	27-43-03-03
ECLASS 12.0	27-43-03-03		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--