

CBC-SP 14-120/25 V2 WT**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Spiral and webbing hoses are particularly suitable for the construction of space-saving cable routing systems in switch gears and control cabinets. They are used for guiding, protecting and bundling cables and wires - for example, in the transition between the enclosure interior and the door.

General ordering data

Version	Protective cable hose coil
Order No.	2588620000
Type	CBC-SP 14-120/25 V2 WT
GTIN (EAN)	4050118602128
Qty.	25 m

Erstellungs-Datum June 1, 2023 10:07:25 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

CBC-SP 14-120/25 V2 WT

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Length	100,000 mm	Length (inches)	3,937 inch
Diameter	12 mm	Net weight	31.92 g

Temperatures

Operating temperature range	-15...60 °C	Operating temperature, min.	-15 °C
Operating temperature, max.	60 °C		

General information

Bundle diameter, max.	120 mm	Bundle diameter, min.	14 mm
Colour	white	Diameter	12 mm
Material	Polyethylene	Nominal diameter	9.6 mm
Operating temperature range	-15...60 °C	UL 94 flammability rating	V-2
Usable cross-section	11,309 mm ²		

Classifications

ETIM 6.0	EC001182	ETIM 7.0	EC001182
ETIM 8.0	EC001182	ECLASS 9.1	27-43-03-03
ECLASS 10.0	27-43-03-03	ECLASS 11.0	27-43-03-03
ECLASS 12.0	27-43-03-03		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--