

CD 100X40 4/6 GY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Version	Cable duct, 100 mm x 40 mm, 4.00 mm x 6.00 mm, 2000 mm
Order No.	2589260000
Type	CD 100X40 4/6 GY
GTIN (EAN)	4050118603088
Qty.	16 m

Erstellungs-Datum June 1, 2023 10:19:30 AM CEST

CD 100X40 4/6 GY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	100 mm	Height (inches)	3.937 inch
Width	40 mm	Width (inches)	1.575 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	819 g		

Temperatures

Operating temperature range	-5...60 °C	Operating temperature, min.	-5 °C
Operating temperature, max.	60 °C		

General information

Colour	grey	Flexible wiring duct	No
Halogen	Yes	Included in delivery	Cable duct, Lid
Lid	Yes	Material	PVC / lead-free
Non-tracking	Yes	Operating temperature range	-5...60 °C
Slit gap	6 mm	Slit width	4 mm
Standards	In accordance with DIN EN 50085	Type of mounting	when screwed in, With adhesive, Riveted
UL 94 flammability rating	V-0	Usable cross-section	3,375 mm ²
Version of side panel	slotted		

Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ECLASS 9.1	27-40-07-03
ECLASS 10.0	27-40-07-03	ECLASS 11.0	27-40-07-03
ECLASS 12.0	27-40-07-03		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E500004

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format

CD 100X40 4/6 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

