

CD-HF 75X75 5/7.5 DKG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Orders on request only

Similar to illustration



The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Version	Halogen-free cable duct, 75 mm x 75 mm, 5.00 mm x 7.50 mm, 2000 mm
Order No.	2589340000
Type	CD-HF 75X75 5/7.5 DKG
GTIN (EAN)	4050118603637
Qty.	16 m

CD-HF 75X75 5/7.5 DKG

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	75 mm	Height (inches)	2.953 inch
Width	75 mm	Width (inches)	2.953 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	675 g		

Temperatures

Operating temperature range	-25...120 °C	Operating temperature, min.	-25 °C
Operating temperature, max.	120 °C		

General information

Colour	dark grey	Flexible wiring duct	No
Halogen	No	Included in delivery	Cable duct, Lid
Lid	Yes	Material	PPE
Non-tracking	Yes	Operating temperature range	-25...120 °C
Slit gap	7.5 mm	Slit width	5 mm
Standards	In accordance with DIN EN 50085	Type of mounting	when screwed in, With adhesive, Riveted
UL 94 flammability rating	V-0	Usable cross-section	4,930 mm ²
Version of side panel	slotted		

Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ECLASS 9.1	27-40-07-03
ECLASS 10.0	27-40-07-03	ECLASS 11.0	27-40-07-03
ECLASS 12.0	27-40-07-03		

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E500004

Downloads

Catalogues [Catalogues in PDF-format](#)

Datenblatt

CD-HF 75X75 5/7.5 DKG

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

