

**CD-HF 50X50 5/7.5 DKG**

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

Orders on request only

**Similar to illustration**



The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

**General ordering data**

|            |  |
|------------|--|
| Version    | Halogen-free cable duct, 50 mm x 50 mm, 5.00 mm x 7.50 mm, 2000 mm |
| Order No.  | <a href="#">2589410000</a>   |
| Type       | CD-HF 50X50 5/7.5 DKG  |
| GTIN (EAN) | 4050118603484  |
| Qty.       | 24 m   |

## CD-HF 50X50 5/7.5 DKG

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

|            |          |                 |            |
|------------|----------|-----------------|------------|
| Height     | 50 mm    | Height (inches) | 1.969 inch |
| Width      | 50 mm    | Width (inches)  | 1.969 inch |
| Length     | 2,000 mm | Length (inches) | 78.74 inch |
| Net weight | 300 g    |                 |            |

### Temperatures

|                             |              |                             |        |
|-----------------------------|--------------|-----------------------------|--------|
| Operating temperature range | -25...120 °C | Operating temperature, min. | -25 °C |
| Operating temperature, max. | 120 °C       |                             |        |

### General information

|                           |                                 |                             |   |
|---------------------------|---------------------------------|-----------------------------|---|
| Colour                    | dark grey                       | Flexible wiring duct        | No                                      |
| Halogen                   | No                              | Included in delivery        | Cable duct, Lid                         |
| Lid                       | Yes                             | Material                    | PPE                                     |
| Non-tracking              | Yes                             | Operating temperature range | -25...120 °C                            |
| Slit gap                  | 7.5 mm                          | Slit width                  | 5 mm                                    |
| Standards                 | In accordance with DIN EN 50085 | Type of mounting            | when screwed in, With adhesive, Riveted |
| UL 94 flammability rating | V-0                             | Usable cross-section        | 2,090 mm <sup>2</sup>                   |
| Version of side panel     | slotted                         |                             |   |

### Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC000012    | ETIM 7.0    | EC000012    |
| ETIM 8.0    | EC000012    | ECLASS 9.1  | 27-40-07-03 |
| ECLASS 10.0 | 27-40-07-03 | ECLASS 11.0 | 27-40-07-03 |
| ECLASS 12.0 | 27-40-07-03 |             |             |

### Approvals

Approvals



|                       |            |
|-----------------------|------------|
| ROHS                  | Conform    |
| UL File Number Search | UL Website |
| Certificate No. (UR)  | E500004    |

### Downloads

Catalogues [Catalogues in PDF-format](#)

**CD-HF 50X50 5/7.5 DKG**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

