


CD-COD 110X110 4/6 GY**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

Version	Cable duct corner duct, 110 mm x 110 mm, 4.00 mm x 6.00 mm, 2000 mm
Order No.	2589460000
Type	CD-COD 110X110 4/6 GY
GTIN (EAN)	4050118601299
Qty.	8 m

Erstellungs-Datum June 1, 2023 10:26:13 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

CD-COD 110X110 4/6 GY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	110 mm	Height (inches)	4.331 inch
Width	110 mm	Width (inches)	4.331 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	1,513 g		

Temperatures

Operating temperature range	-5...60 °C	Operating temperature, min.	-5 °C
Operating temperature, max.	60 °C		

General information

Colour	grey	Flexible wiring duct	No
Halogen	Yes	Included in delivery	Cable duct, Lid
Lid	Yes	Material	PVC / lead-free
Non-tracking	Yes	Operating temperature range	-5...60 °C
Slit gap	6 mm	Slit width	4 mm
Standards	In accordance with DIN EN 50085	Type of mounting	when screwed in, With adhesive, Riveted
UL 94 flammability rating	V-0	Usable cross-section	11,020 mm ²
Version of side panel	slotted		

Classifications

ETIM 6.0	EC001942	ETIM 7.0	EC001942
ETIM 8.0	EC001942	ECLASS 9.1	27-40-07-07
ECLASS 10.0	27-40-07-07	ECLASS 11.0	27-40-07-07
ECLASS 12.0	27-40-07-07		

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format