

CD 75X25 5/7.5 GY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

| | |
|------------|---|
| Version | Cable duct, 75 mm x 25 mm, 5.00 mm x 7.50 mm, 2000 mm |
| Order No. | 2589580000 |
| Type | CD 75X25 5/7.5 GY |
| GTIN (EAN) | 4050118603279 |
| Qty. | 32 m |

Erstellungs-Datum June 1, 2023 10:27:59 AM CEST

CD 75X25 5/7.5 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Height | 75 mm | Height (inches) | 2.953 inch |
| Width | 25 mm | Width (inches) | 0.984 inch |
| Length | 2,000 mm | Length (inches) | 78.74 inch |
| Net weight | 406 g | | |

Temperatures

| | | | |
|-----------------------------|------------|-----------------------------|-------|
| Operating temperature range | -5...60 °C | Operating temperature, min. | -5 °C |
| Operating temperature, max. | 60 °C | | |

General information

| | | | |
|---------------------------|---------------------------------|-----------------------------|---|
| Colour | grey | Flexible wiring duct | No |
| Halogen | Yes | Included in delivery | Cable duct, Lid |
| Lid | Yes | Material | PVC / lead-free |
| Non-tracking | Yes | Operating temperature range | -5...60 °C |
| Slit gap | 7.5 mm | Slit width | 5 mm |
| Standards | In accordance with DIN EN 50085 | Type of mounting | when screwed in, With adhesive, Riveted |
| UL 94 flammability rating | V-0 | Usable cross-section | 1,485 mm ² |
| Version of side panel | slotted | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000012 | ETIM 7.0 | EC000012 |
| ETIM 8.0 | EC000012 | ECLASS 9.1 | 27-40-07-03 |
| ECLASS 10.0 | 27-40-07-03 | ECLASS 11.0 | 27-40-07-03 |
| ECLASS 12.0 | 27-40-07-03 | | |

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E500004 |

Downloads

Catalogues [Catalogues in PDF-format](#)

Datenblatt

CD 75X25 5/7.5 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

