

CD-HF 75X50 5/7.5 LTGY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

| | |
|------------|--|
| Version | Halogen-free cable duct, 75 mm x 50 mm, 5.00 mm x 7.50 mm, 2000 mm |
| Order No. | 2589780000 |
| Type | CD-HF 75X50 5/7.5 LTGY |
| GTIN (EAN) | 4050118603347 |
| Qty. | 24 m |

CD-HF 75X50 5/7.5 LTGY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Height | 75 mm | Height (inches) | 2.953 inch |
| Width | 50 mm | Width (inches) | 1.969 inch |
| Length | 2,000 mm | Length (inches) | 78.74 inch |
| Net weight | 437.5 g | | |

Temperatures

| | | | |
|-----------------------------|--------------|-----------------------------|--------|
| Operating temperature range | -25...105 °C | Operating temperature, min. | -25 °C |
| Operating temperature, max. | 105 °C | | |

General information

| | | | |
|---------------------------|---------------------------------|-----------------------------|---|
| Colour | Light Grey | Flexible wiring duct | No |
| Halogen | No | Included in delivery | Cable duct, Lid |
| Lid | Yes | Material | PC-ABS |
| Non-tracking | Yes | Operating temperature range | -25...105 °C |
| Slit gap | 7.5 mm | Slit width | 5 mm |
| Standards | In accordance with DIN EN 50085 | Type of mounting | when screwed in, With adhesive, Riveted |
| UL 94 flammability rating | V-0 | Usable cross-section | 3,200 mm ² |
| Version of side panel | slotted | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000012 | ETIM 7.0 | EC000012 |
| ETIM 8.0 | EC000012 | ECLASS 9.1 | 27-40-07-03 |
| ECLASS 10.0 | 27-40-07-03 | ECLASS 11.0 | 27-40-07-03 |
| ECLASS 12.0 | 27-40-07-03 | | |

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E500004 |

Downloads

Catalogues [Catalogues in PDF-format](#)

Datenblatt

CD-HF 75X50 5/7.5 LTGY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

