

CD-BO 80X60 8/12 GY

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



The broad range of cable ducts offers you a flexible wire management system in a constant quality. The accurately sizes of the punched holes in accordance to DIN EN 50085-2-3 enables you a precise installation. Next to wire holding lugs as fixing aid for already installed wires, the optimal closing mechanism provide an easy snapping as well as a safe fit of the lid.

General ordering data

| | |
|------------|---|
| Version | Cable duct floor duct, 80 mm x 60 mm, 8.00 mm x 12.00 mm, 2000 mm |
| Order No. | 2589840000 |
| Type | CD-BO 80X60 8/12 GY |
| GTIN (EAN) | 4050118600919 |
| Qty. | 24 m |

Erstellungs-Datum June 1, 2023 10:32:56 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

CD-BO 80X60 8/12 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Height | 80 mm | Height (inches) | 3.15 inch |
| Width | 60 mm | Width (inches) | 2.362 inch |
| Length | 2,000 mm | Length (inches) | 78.74 inch |
| Net weight | 729 g | | |

Temperatures

| | | | |
|-----------------------------|------------|-----------------------------|-------|
| Operating temperature range | -5...60 °C | Operating temperature, min. | -5 °C |
| Operating temperature, max. | 60 °C | | |

General information

| | | | |
|-----------------------------|---|---------------------------|---------------------------------|
| Colour | grey | Flexible wiring duct | No |
| Floor rails | 1 | Halogen | Yes |
| Included in delivery | Cable duct, Lid | Lid | Yes |
| Material | PVC / lead-free | Non-tracking | Yes |
| Operating temperature range | -5...60 °C | Slit gap | 12 mm |
| Slit width | 8 mm | Standards | In accordance with DIN EN 50085 |
| Type of mounting | when screwed in, With adhesive, Riveted | UL 94 flammability rating | V-0 |
| Usable cross-section | 4,175 mm ² | Version of side panel | slotted |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000012 | ETIM 7.0 | EC000012 |
| ETIM 8.0 | EC000012 | ECLASS 9.1 | 27-40-07-03 |
| ECLASS 10.0 | 27-40-07-03 | ECLASS 11.0 | 27-40-07-03 |
| ECLASS 12.0 | 27-40-07-03 | | |

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E500004 |

Downloads

Catalogues [Catalogues in PDF-format](#)

Datenblatt

CD-BO 80X60 8/12 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

