

## CD-LID 120 GY

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

### Similar to illustration



Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

### General ordering data

Version	Cable duct cover, 120 mm
Order No.	<a href="#">2589990000</a>
Type	CD-LID 120 GY
GTIN (EAN)	4050118600773
Qty.	2 m

## CD-LID 120 GY

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Width	120 mm	Width (inches)	4.724 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	305 g		

### Temperatures

Operating temperature range	-5...60 °C	Operating temperature, min.	-5 °C
Operating temperature, max.	60 °C		

### General information

Colour	grey	Flexible wiring duct	No
Halogen	Yes	Lid	Yes
Material	PVC / lead-free	Non-tracking	Yes
Operating temperature range	-5...60 °C	Type of mounting	Snap-on
UL 94 flammability rating	V-0		

### Classifications

ETIM 6.0	EC000727	ETIM 7.0	EC000727
ETIM 8.0	EC000727	ECLASS 9.1	27-40-07-76
ECLASS 10.0	27-40-07-76	ECLASS 11.0	27-40-07-76
ECLASS 12.0	27-40-07-76		

### Approvals

ROHS	Conform
------	---------

### Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--