

CD-LID 25 GY

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration



Increase your wiring flexibility with our comprehensive range of accessories available from a single source.

General ordering data

| | |
|------------|----------------------------|
| Version | Cable duct cover, 25 mm |
| Order No. | 2590110000 |
| Type | CD-LID 25 GY |
| GTIN (EAN) | 4050118600650 |
| Qty. | 2 m |

CD-LID 25 GY

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|----------|-----------------|------------|
| Width | 25 mm | Width (inches) | 0.984 inch |
| Length | 2,000 mm | Length (inches) | 78.74 inch |
| Net weight | 55 g | | |

Temperatures

| | | | |
|-----------------------------|------------|-----------------------------|-------|
| Operating temperature range | -5...60 °C | Operating temperature, min. | -5 °C |
| Operating temperature, max. | 60 °C | | |

General information

| | | | |
|-----------------------------|-----------------|----------------------|---------|
| Colour | grey | Flexible wiring duct | No |
| Halogen | Yes | Lid | Yes |
| Material | PVC / lead-free | Non-tracking | Yes |
| Operating temperature range | -5...60 °C | Type of mounting | Snap-on |
| UL 94 flammability rating | V-0 | | |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000727 | ETIM 7.0 | EC000727 |
| ETIM 8.0 | EC000727 | ECLASS 9.1 | 27-40-07-76 |
| ECLASS 10.0 | 27-40-07-76 | ECLASS 11.0 | 27-40-07-76 |
| ECLASS 12.0 | 27-40-07-76 | | |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

Catalogues [Catalogues in PDF-format](#)