

SM-FO 27/8 MM WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Prevention of incorrect operation: SM**

MultiMark device markers can be used with marking materials from different manufacturers. Wherever they are used, they ensure that all components, such as control and signalling devices from different vendors, are clearly assigned.

Your benefits with MultiMark

- "Different materials for various requirements"
- Can be used with equipment from many manufacturers
- Device markers with a familiar design

General ordering data

| | |
|--------------------|-------------------------------------------------------|
| Version | SwitchMark, Device markers, 8 x 27 mm, white |
| Order No. | 2621070000 |
| Type | SM-FO 27/8 MM WS |
| GTIN (EAN) | 4050118625974 |
| Qty. | 500 Stück |
| compatible printer | 2599430000 2599440000 |

Erstellungs-Datum June 2, 2023 12:31:54 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

SM-FO 27/8 MM WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|---------|-----------------|------------|
| Depth | 0.55 mm | Depth (inches) | 0.022 inch |
| Height | 8 mm | Height (inches) | 0.315 inch |
| Width | 27 mm | Width (inches) | 1.063 inch |
| Net weight | 0.03 g | | |

Temperatures

| | |
|-----------------------------|-------------|
| Operating temperature range | -30...80 °C |
|-----------------------------|-------------|

General data

| | | | |
|-----------------------------------|-------------------------------|-----------------------------------|-----------------------------|
| Adhesive | PE-foam with acrylic adhesive | Approval acc. to UL 969 | Yes |
| Colour | white | Halogen | No |
| Material | Polyester | Number per roll | 500 |
| Operating temperature range | -30...80 °C | Operating temperature range, max. | 80 °C |
| Operating temperature range, min. | -30 °C | Size of labelling field | 8 x 27 mm |
| UL 94 flammability rating | V-0 | Version | halogen-free, Self-adhesive |
| Width | 27 mm | | |

Device markers

| | |
|---------|----|
| Halogen | No |
|---------|----|

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001288 | ETIM 7.0 | EC001288 |
| ETIM 8.0 | EC001288 | ECLASS 9.0 | 27-40-06-29 |
| ECLASS 9.1 | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|------------------|------------------------------------------|
| Engineering Data | EPLAN |
| Catalogues | Catalogues in PDF-format |

Datenblatt

SM-FO 27/8 MM WS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

