

**THM WO 20/32 WS****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

**General ordering data**

Version	THM, Conductor and cable markers, 2.8 - 7 mm, 20 x 32 mm, white
Order No.	<a href="#">2621500000</a>
Type	THM WO 20/32 WS
GTIN (EAN)	4050118625547
Qty.	3,000 Stück
compatible printer	<a href="#">2599430000</a> <a href="#">2599440000</a>

Erstellungs-Datum June 2, 2023 12:37:27 PM CEST

## THM WO 20/32 WS

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	20 mm	Height (inches)	0.787 inch
Width	32 mm	Width (inches)	1.26 inch
Net weight	0.117 g		

### Temperatures

Operating temperature range	-40...
-----------------------------	--------

### General data

Colour	white	Number of markers per combination	1 Label reel = Conductor and cable markers
Operating temperature range	-40...	Operating temperature range, min.	-40 °C
Size of labelling field	9 x 20 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Width	32 mm

### Conductor and cable markers

Conductor O.D.	2.8 - 7 mm	Conductor O.D., max.	7 mm
Conductor O.D., min.	2.8 mm		

### Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">EPLAN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

