

THM WO 25/37 WS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



THM WriteOn cable markers on reels are used for labelling conductors and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.

- Protection of the marking against dirt and abrasion by wrapping it with the transparent adhesive strip
- Simple and quick printing with the high-quality thermal transfer printers

General ordering data

Version	THM, Conductor and cable markers, 4.8 - 7 mm, 25 x 37 mm, white
Order No.	2621510000
Type	THM WO 25/37 WS
GTIN (EAN)	4050118625530
Qty.	2,500 Stück
compatible printer	2599430000 2599440000

Erstellungs-Datum June 2, 2023 12:37:36 PM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

THM WO 25/37 WS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	0.025 mm	Depth (inches)	0.001 inch
Height	25 mm	Height (inches)	0.984 inch
Width	37 mm	Width (inches)	1.457 inch
Net weight	0.16 g		

Temperatures

Operating temperature range	-40...
-----------------------------	--------

General data

Colour	white	Number of markers per combination	1 Label reel = Conductor and cable markers
Operating temperature range	-40...	Operating temperature range, min.	-40 °C
Size of labelling field	15 x 25 mm	Type of printing	neutral
UL 94 flammability rating	V-0	Width	37 mm

Conductor and cable markers

Conductor O.D.	4.8 - 7 mm	Conductor O.D., max.	7 mm
Conductor O.D., min.	4.8 mm		

Classifications

ETIM 6.0	EC001288	ETIM 7.0	EC001288
ETIM 8.0	EC001288	ECLASS 9.0	27-40-06-29
ECLASS 9.1	27-40-06-29	ECLASS 10.0	27-40-06-29
ECLASS 11.0	27-28-11-04	ECLASS 12.0	27-28-11-04

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format

Zeichnungen

