

CABTITE BP 14MM PA

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



The blanking plugs are used for the safe closing of unneeded cable passages in the sealing elements.

General ordering data

Version	Blind plug, Cabtite (cable entry system), Polyamide, white, Height: 22 mm, Width: 14 mm, Depth: 22 mm, -40 °C...120 °C, IP66
Order No.	2652420000
Type	CABTITE BP 14MM PA
GTIN (EAN)	4050118662528
Qty.	25 Stück

Erstellungs-Datum May 26, 2023 2:27:51 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

CABTITE BP 14MM PA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	22 mm	Depth (inches)	0.866 inch
Height	22 mm	Height (inches)	0.866 inch
Width	14 mm	Width (inches)	0.551 inch
Length	22 mm	Length (inches)	0.866 inch
Diameter	14 mm	Net weight	0.056 g

Temperatures

Operating temperature	-40 °C...120 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	120 °C		

General information

Halogen	No	Material	Polyamide
Outer cable diameter, max.	14 mm	Outer cable diameter, min.	14 mm
Protection degree	IP66	UL 94 flammability rating	V-0

Classifications

ETIM 6.0	EC000879	ETIM 7.0	EC000879
ETIM 8.0	EC000879	ECLASS 9.0	27-14-44-21
ECLASS 9.1	27-14-44-21	ECLASS 10.0	27-14-44-21
ECLASS 11.0	27-14-44-21	ECLASS 12.0	27-14-08-07

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN
User Documentation	Cabtite Installation Instructions
Catalogues	Catalogues in PDF-format