

CABTITE BP 25MM PA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Similar to illustration



Similar to illustration

The blanking plugs are used for the safe closing of unneeded cable passages in the sealing elements.

General ordering data

Version	Blind plug, Cabtite (cable entry system), Polyamide, red, Height: 30 mm, Width: 25 mm, Depth: 30 mm, -60 °C...100 °C, IP66
Order No.	2652460000
Type	CABTITE BP 25MM PA
GTIN (EAN)	4050118662566
Qty.	50 Stück

Erstellungs-Datum May 26, 2023 2:28:36 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

CABTITE BP 25MM PA

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	30 mm	Depth (inches)	1.181 inch
Height	30 mm	Height (inches)	1.181 inch
Width	25 mm	Width (inches)	0.984 inch
Length	30 mm	Length (inches)	1.181 inch
Diameter	25 mm	Net weight	2.1 g

Temperatures

Operating temperature	-60 °C...100 °C	Operating temperature, min.	-60 °C
Operating temperature, max.	100 °C		

General information

Halogen	No	Material	Polyamide
Outer cable diameter, max.	25 mm	Outer cable diameter, min.	25 mm
Protection degree	IP66	UL 94 flammability rating	V-0

Classifications

ETIM 6.0	EC000879	ETIM 7.0	EC000879
ETIM 8.0	EC000879	ECLASS 9.0	27-14-44-21
ECLASS 9.1	27-14-44-21	ECLASS 10.0	27-14-44-21
ECLASS 11.0	27-14-44-21	ECLASS 12.0	27-14-08-07

Approvals

ROHS	Conform
------	---------

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN
User Documentation	Cabtite Installation Instructions
Catalogues	Catalogues in PDF-format