

## KCMA-RCM-58D


**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)



### **Difference current transformer** (Residual current monitoring, RCM)

This type is specialised in the detection of residual currents in 3 / 4-wire AC networks.

Its special features are:

Highly sensitive current sensor for the detection of even the smallest residual currents, fixed switching hysteresis of 5%, high safety thanks to integrated overvoltage protection and coverage of a wide frequency range.

### **General ordering data**

Version	Residual current transformer (RCM), Primary current: 18 A, Round conductor: 50.00 mm, Split-core current transformer
Order No.	<a href="#">2656280000</a>
Type	KCMA-RCM-58D
GTIN (EAN)	4050118666359
Qty.	1 Stück

Erstellungs-Datum June 5, 2023 10:07:27 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## KCMA-RCM-58D

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	158 mm	Depth (inches)	6.22 inch
Width	58 mm	Width (inches)	2.283 inch
Length	125 mm	Length (inches)	4.921 inch
Net weight	240 g		

### Temperatures

Operating temperature	-5 °C...45 °C	Operating temperature, min.	-5 °C
Operating temperature, max.	45 °C		

### Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	50 mm
Rail	50 x 80 mm	Installation location	Indoor use

### Electrical attributes

Frequency band	30...1000 Hz	Primary conductor temperature	70 °C
Primary current	18 A	Secondary current	0...30 mA
Secondary current, min.	0.03 A	Tolerance class	1
Transmission ratio	1:600		

### Insulation coordination

Standard	EN 60044/1	Tolerance class	1
----------	------------	-----------------	---

### Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ECLASS 9.0	27-21-09-02
ECLASS 9.1	27-21-09-02	ECLASS 10.0	27-21-09-02
ECLASS 11.0	27-21-09-02	ECLASS 12.0	27-21-09-02

### Approvals

ROHS	Conform
------	---------

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">EU Declaration of Conformity</a>
User Documentation	<a href="#">Instruction sheet english</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

KCMA-RCM-58D

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

Zeichnungen

Dimensional drawing

