

KCMA-RCM-812D**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Difference current transformer** (Residual current monitoring, RCM)

This type is specialised in the detection of residual currents in 3 / 4-wire AC networks.

Its special features are:

Highly sensitive current sensor for the detection of even the smallest residual currents, fixed switching hysteresis of 5%, high safety thanks to integrated overvoltage protection and coverage of a wide frequency range.

General ordering data

Version	Residual current transformer (RCM), Primary current: 18 A, Round conductor: 80.00 mm, Split-core current transformer
Order No.	2656290000
Type	KCMA-RCM-812D
GTIN (EAN)	4050118666342
Qty.	1 Stück

Erstellungs-Datum June 5, 2023 10:07:36 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

KCMA-RCM-812D

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	198 mm	Depth (inches)	7.795 inch
Width	58 mm	Width (inches)	2.283 inch
Length	155 mm	Length (inches)	6.102 inch
Net weight	240 g		

Temperatures

Operating temperature	-5 °C...45 °C	Operating temperature, min.	-5 °C
Operating temperature, max.	45 °C		

Dimensions of live conductors

Type of conductor	Insulated conductor only	Round conductor	80 mm
Rail	80 x 120 mm	Installation location	Indoor use

Electrical attributes

Frequency band	30...1000 Hz	Primary conductor temperature	70 °C
Primary current	18 A	Secondary current	0...30 mA
Secondary current, min.	0.03 A	Tolerance class	1
Transmission ratio	1:600		

Insulation coordination

Standard	EN 60044/1	Tolerance class	1
----------	------------	-----------------	---

Classifications

ETIM 6.0	EC002048	ETIM 7.0	EC002048
ETIM 8.0	EC002048	ECLASS 9.0	27-21-09-02
ECLASS 9.1	27-21-09-02	ECLASS 10.0	27-21-09-02
ECLASS 11.0	27-21-09-02	ECLASS 12.0	27-21-09-02

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	EU Declaration of Conformity
User Documentation	Instruction sheet english
Catalogues	Catalogues in PDF-format

KCMA-RCM-812D

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

Dimensional drawing

