


**G-2L+9-1000/10****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

Similar to illustration

2-pole fork-type phase distribution bars are used for potential distribution to other components in the control cabinet such as circuit breakers, residual current circuit breakers and other installation devices.

**General ordering data**

Order No.	<a href="#">2658170000</a>
Type	G-2L+9-1000/10
GTIN (EAN)	4050118672350
Qty.	5 Stück

## G-2L+9-1000/10

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	9.3 mm	Depth (inches)	0.366 inch
Height	28.5 mm	Height (inches)	1.122 inch
Width	1,016 mm	Width (inches)	40 inch
Net weight	315 g		

### Material data

Colour	grey
--------	------

### Dimensions

Pitch in mm (P)	17.8 mm
-----------------	---------

### General

Number of poles	46
-----------------	----

### Rating data

Rated cross-section	10 mm <sup>2</sup>	Rated current	63 A
---------------------	--------------------	---------------	------

### Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

### Approvals

Approvals



ROHS Conform

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">CE Declaration of Conformity</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Datenblatt**

**G-2L+9-1000/10**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Drawing**

