


**G-4L-140/16 C****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

4-pole fork-type phase distribution bars are used for potential distribution to other components in the control cabinet such as circuit breakers, residual current circuit breakers and other installation devices.

**General ordering data**

Order No.	<a href="#">265870000</a>
Type	G-4L-140/16 C
GTIN (EAN)	4050118671827
Qty.	5 Stück

## G-4L-140/16 C

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	20.2 mm	Depth (inches)	0.795 inch
Height	28.5 mm	Height (inches)	1.122 inch
Width	140 mm	Width (inches)	5.512 inch
Net weight	83 g		

### Material data

Colour	grey
--------	------

### Dimensions

Pitch in mm (P)	17.8 mm
-----------------	---------

### General

Number of poles	8
-----------------	---

### Rating data

Rated cross-section	16 mm <sup>2</sup>	Rated current	80 A
---------------------	--------------------	---------------	------

### Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

### Approvals

Approvals



ROHS Conform

### Downloads

Approval/Certificate/Document of Conformity	<a href="#">CE Declaration of Conformity</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>

**Datenblatt**

**G-4L-140/16 C**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Drawing**

