

FIT 25 GN**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com**Product image**

Our feed-in modules facilitate handling when feeding the system. For example, the bending radius of the cable can be reduced by using a feed-in module with side entry.

General ordering data

Order No.	2659050000
Type	FIT 25 GN
GTIN (EAN)	4050118671483
Qty.	10 Stück

FIT 25 GN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	19.5 mm	Depth (inches)	0.768 inch
Height	34 mm	Height (inches)	1.339 inch
Width	13.5 mm	Width (inches)	0.531 inch
Net weight	10 g		

Material data

Colour	grey
--------	------

Rating data

Rated cross-section	25 mm ²	Rated current	101 A
---------------------	--------------------	---------------	-------

Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--