

**FIT 50 GN****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Product image**

Our feed-in modules facilitate handling when feeding the system. For example, the bending radius of the cable can be reduced by using a feed-in module with side entry.

**General ordering data**

Order No.	<a href="#">2659070000</a>
Type	FIT 50 GN
GTIN (EAN)	4050118671469
Qty.	3 Stück

## FIT 50 GN

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	27 mm	Depth (inches)	1.063 inch
Height	39.7 mm	Height (inches)	1.563 inch
Width	17.8 mm	Width (inches)	0.701 inch
Net weight	28 g		

### Material data

Colour	grey
--------	------

### General

Number of poles	1
-----------------	---

### Rating data

Rated cross-section	50 mm <sup>2</sup>	Rated current	150 A
---------------------	--------------------	---------------	-------

### Classifications

ETIM 6.0	EC002848	ETIM 7.0	EC002848
ETIM 8.0	EC002848	ECLASS 9.0	27-14-11-92
ECLASS 9.1	27-14-11-92	ECLASS 10.0	27-14-11-92
ECLASS 11.0	27-14-11-92	ECLASS 12.0	27-14-11-92

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	08c53393-8863-492c-addc-d040b46da0d3

### Approvals

ROHS	Conform
------	---------

### Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--