


**CB-HTR 290/4,5 BK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Our heat-stabilised cable ties made of polyamide 6.6 are suitable for continuous use at temperatures up to +125°C.

**General ordering data**

Version	Cable ties, 4.5 x 290 mm, Polyamide 66, 220 N
Order No.	<a href="#">2659410000</a>
Type	CB-HTR 290/4,5 BK
GTIN (EAN)	4050118682878
Qty.	100 Stück

Erstellungs-Datum May 26, 2023 2:52:54 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## CB-HTR 290/4,5 BK

**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Dimensions and weights

Height	290 mm	Height (inches)	11.417 inch
Width	4.5 mm	Width (inches)	0.177 inch
Net weight	1.9 g		

### Temperatures

Operating temperature range	-40...125 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	125 °C	Continuous operating temp., min.	-40 °C
Continuous operating temp., max.	125 °C		

### Installation materials

Bundle diameter, max.	78 mm	Bundle diameter, min.	3.5 mm
Cable diameter, max.	79 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	125 °C	Operating temperature range, min.	-40 °C
Tensile strength	220 N	Tensile strength (Pound-force)	49 lbf
UL 94 flammability rating	V-2	UV-resistant	No

### Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

### Approvals

Approvals



ROHS

Conform

### Downloads

Approval/Certificate/Document of Conformity

[EU Declaration of Conformity](#)

Catalogues

[Catalogues in PDF-format](#)

**Datenblatt**

**CB-HTR 290/4,5 BK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

