

CD 80X100 4/6 BL**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Well-structured and protected wiring provides the basis for installation, maintenance, and safe operation. Those requirements apply in particular for explosion-protected areas. According to DIN EN 60079-14 these wiring ducts are suitable for cables containing intrinsically safe circuits.

General ordering data

Version	80 mm x 100 mm, 4.00 mm x 6.00 mm, 2000 mm
Order No.	2662570000
Type	CD 80X100 4/6 BL
GTIN (EAN)	4050118685145
Qty.	16 m

Erstellungs-Datum May 26, 2023 2:59:19 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

CD 80X100 4/6 BL

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	80 mm	Height (inches)	3.15 inch
Width	100 mm	Width (inches)	3.937 inch
Length	2,000 mm	Length (inches)	78.74 inch
Net weight	1,056.431 g		

Temperatures

Operating temperature range	-5...60 °C	Operating temperature, min.	-5 °C
Operating temperature, max.	60 °C		

General information

Colour	blue	Halogen	Yes
Included in delivery	Cable duct, Lid	Lid	Yes
Material	PVC / lead-free	Operating temperature range	-5...60 °C
Slit gap	6 mm	Slit width	4 mm
Standards	In accordance with DIN EN 50085	UL 94 flammability rating	V-0
Version of side panel	slotted		

Classifications

ETIM 6.0	EC000012	ETIM 7.0	EC000012
ETIM 8.0	EC000012	ECLASS 9.1	27-40-07-03
ECLASS 10.0	27-40-07-03	ECLASS 11.0	27-40-07-03
ECLASS 12.0	27-40-07-03		

Approvals

ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--