

**HDC XX6A01 OOXXXDM-1000****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

**General ordering data**

Version	
Order No.	<a href="#">2712671000</a>
Type	HDC XX6A01 OOXXXDM-1000
GTIN (EAN)	4050118753011
Qty.	1 Stück

Erstellungs-Datum June 5, 2023 10:25:58 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## HDC XX6A01 OOXXXDM-1000

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Net weight 3,800 g

### Temperatures

Operating temperature, min. -50 °C      Operating temperature, max. 70 °C

### General data

Cable length	100 m	Category	Cat.7 (ISO/IEC 11801)
Module side version	open	Number of poles	8
Opposite side version	open	Pollution severity	2
Rated current	0.5 A	Rated voltage	50 V

### Cable technical specifications

Cable length 100 m      Halogen No

### Classifications

ETIM 6.0	EC000830	ETIM 7.0	EC003249
ETIM 8.0	EC003249	ECLASS 9.0	27-06-18-05
ECLASS 9.1	27-06-90-90	ECLASS 10.0	27-06-18-01
ECLASS 11.0	27-06-18-01	ECLASS 12.0	27-06-18-01

### Approvals

ROHS Conform

### Downloads

Catalogues [Catalogues in PDF-format](#)