

HDC XX6A02 OOXXXDM-1000**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

**Compact**

The new two-pole bus module is extremely compact and can accommodate both megabit and gigabit data inserts. It enables the connection of 2 Gigabit Cat 6A cables (10 gigabit) to one module.

General ordering data

Version	
Order No.	2712681000
Type	HDC XX6A02 OOXXXDM-1000
GTIN (EAN)	4050118753028
Qty.	1 Stück

Erstellungs-Datum June 5, 2023 10:26:07 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

HDC XX6A02 OOXXXDM-1000

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 2,300 g

Temperatures

Operating temperature, min. -40 °C Operating temperature, max. 80 °C

General data

Cable length	100 m	Category	Cat.7 (ISO/IEC 11801)
Insulation strength	≥ 500 MΩ	Module side version	open
Number of poles	8	Opposite side version	open
Pollution severity	2	Rated current	0.5 A
Rated voltage	100 V		

Cable technical specifications

Cable length	100 m	Halogen	halogen-free, according to IEC 60754-1
Insulation	PE	Sheath material	PUR
Sheathing colour	green		

Classifications

ETIM 6.0	EC000830	ETIM 7.0	EC003249
ETIM 8.0	EC003249	ECLASS 9.0	27-06-18-05
ECLASS 9.1	27-06-90-90	ECLASS 10.0	27-06-18-01
ECLASS 11.0	27-06-18-01	ECLASS 12.0	27-06-18-01

Approvals

ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)