


QB 4 MK3**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Product image

Similar to illustration

Screwable cross-connections are easy to mount and de mount. Thanks to the big contact surface, even high currents can be transmitted with maximum contact reliability.

General ordering data

Order No.	3833800000
Type	QB 4 MK3
GTIN (EAN)	4008190542542
Qty.	20 Stück

QB 4 MK3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	3 mm	Depth (inches)	0.118 inch
Height	12.24 mm	Height (inches)	0.482 inch
Width	33.5 mm	Width (inches)	1.319 inch
Net weight	1.573 g		

Temperatures

Storage temperature	-25 °C...55 °C
---------------------	----------------

Material data

Material	PA 6.6	Colour	black
----------	--------	--------	-------

System specifications

Version	Cross-connector
---------	-----------------

Additional technical data

Explosion-tested version	No	Type of fixing	Plugged
Type of mounting	Plugged		

Cross-connector

Rated current, multi-pole	24 A	Type	Cross-connector
---------------------------	------	------	-----------------

Dimensions

Pitch in mm (P)	10 mm
-----------------	-------

General

Number of poles	4
-----------------	---

Rating data

Rated current	24 A
---------------	------

Classifications

ETIM 6.0	EC000489	ETIM 7.0	EC000489
ETIM 8.0	EC000489	ECLASS 9.0	27-14-11-40
ECLASS 9.1	27-14-11-40	ECLASS 10.0	27-14-11-40
ECLASS 11.0	27-14-11-40	ECLASS 12.0	27-14-11-40

Approvals

ROHS	Conform
------	---------

QB 4 MK3

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technische Daten

Downloads

Engineering Data	CAD data – STEP
Engineering Data	EPLAN
User Documentation	StorageConditionsTerminalBlocks
Catalogues	Catalogues in PDF-format