

RKDG D11 PT6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Intelligent cabling solutions can save you valuable time and money.

The FieldPower® modular system contains the right solution for every cabling task.

Foldable seals for the use of pre-assembled cables

Seals available with M16 and M20 connection thread

Integration of operating and signalling devices into the seal possible

General ordering data

Version	Field Power® sealing insert, Foldable seal, IP65 with corresponding housing, IP65, with corresponding enclosure, EPDM, 9 mm, 11 mm
Order No.	4323210000
Type	RKDG D11 PT6
GTIN (EAN)	4032248641215
Qty.	10 Stück

Erstellungs-Datum May 25, 2023 11:53:19 AM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

RKDG D11 PT6

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	18 mm	Depth (inches)	0.709 inch
Height	33.8 mm	Height (inches)	1.331 inch
Width	46.7 mm	Width (inches)	1.839 inch
Net weight	25 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...85 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	85 °C

General data

Clamping range, max.	11 mm	Clamping range, min.	9 mm
Colour	black	Design	Foldable seal
Line type	round	Material	EPDM
Mounting position, installation notice	in FieldPower® sealing slot	Protection degree	IP65 with corresponding housing, IP65, with corresponding enclosure
Silicone	No	UL 94 flammability rating	HB

General data

Material	EPDM	Silicone	No
Colour	black	Design	Foldable seal
Protection degree	IP65 with corresponding housing, IP65, with corresponding enclosure	UL 94 flammability rating	HB
Mounting position, installation notice	in FieldPower® sealing slot	Line type	round
Clamping range, min.	9 mm	Clamping range, max.	11 mm

Classifications

ETIM 6.0	EC002624	ETIM 7.0	EC002624
ETIM 8.0	EC002624	ECLASS 9.1	27-18-27-90
ECLASS 10.0	27-18-28-15	ECLASS 11.0	27-18-28-15
ECLASS 12.0	27-18-28-15		

Approvals

ROHS	Conform
------	---------

Downloads

Approval/Certificate/Document of Conformity	UL Certificate FieldPower® Box and accessories Manufacturer's Declaration FieldPower® Enclosure parts
Engineering Data	CAD data – STEP
Engineering Data	EPLAN
Catalogues	Catalogues in PDF-format