

RS PLC IPC-620 12-POINTS**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



With increasing plant complexity, the obsolescence of certain PLCs and the relentless growth in demand for I / O signals, many installations or plants are having to replace existing controllers with new ones, without modifying existing field cabling. With the aid of adapters, pre-assembled cables and interfaces from Weidmüller the problem of replacing one PLC system with another can be solved easily and safely: users can maintain the existing field cabling, test the new system and keep installation downtimes to a minimum.

General ordering data

Order No.	6720000787
Type	RS PLC IPC-620 12-POINTS
GTIN (EAN)	4050118485790
Qty.	1 Stück

RS PLC IPC-620 12-POINTS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	61 mm	Depth (inches)	2.402 inch
Height	266 mm	Height (inches)	10.472 inch
Width	29 mm	Width (inches)	1.142 inch
Net weight	100 g		

Temperatures

Storage temperature	0...50 °C	Operating temperature	0...50 °C
Operating temperature, min.	0 °C	Operating temperature, max.	50 °C

Ratings data

Operating voltage	150 V	Max. current per channel	5 A
-------------------	-------	--------------------------	-----

Classifications

ETIM 6.0	EC002780	ETIM 7.0	EC002780
ETIM 8.0	EC002780	ECLASS 9.0	27-14-11-52
ECLASS 9.1	27-24-22-92	ECLASS 10.0	27-14-11-52
ECLASS 11.0	27-14-11-52	ECLASS 12.0	27-14-11-52

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	3820ceea-2b49-4a61-bda5-08f3867b3419

Approvals

Approvals



ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)

