

CB 250/4,8 BK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

| | |
|------------|---|
| Version | Cable ties, 4.8 x 250 mm, Polyamide 66, 220 N |
| Order No. | 7940006055 |
| Type | CB 250/4,8 BK |
| GTIN (EAN) | 4032248520206 |
| Qty. | 100 Stück |

Erstellungs-Datum June 1, 2023 11:25:55 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

CB 250/4,8 BK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Depth | 1.4 mm | Depth (inches) | 0.055 inch |
| Height | 250 mm | Height (inches) | 9.842 inch |
| Width | 4.8 mm | Width (inches) | 0.189 inch |
| Net weight | 1.66 g | | |

Temperatures

| | | | |
|-----------------------------|-------------|-----------------------------|--------|
| Operating temperature range | -40...85 °C | Operating temperature, min. | -40 °C |
| Operating temperature, max. | 85 °C | | |

Installation materials

| | | | |
|-----------------------------------|-------|-----------------------------------|--------------|
| Bundle diameter, max. | 68 mm | Bundle diameter, min. | 3 mm |
| Cable diameter, max. | 68 mm | For re-opening | No |
| Halogen | No | Material | Polyamide 66 |
| Operating temperature range, max. | 85 °C | Operating temperature range, min. | -40 °C |
| Tensile strength | 220 N | Tensile strength (Pound-force) | 49 lbf |
| UL 94 flammability rating | V-2 | UV-resistant | No |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC000046 | ETIM 7.0 | EC000046 |
| ETIM 8.0 | EC000046 | ECLASS 9.0 | 27-14-07-02 |
| ECLASS 9.1 | 27-14-07-02 | ECLASS 10.0 | 27-14-07-02 |
| ECLASS 11.0 | 27-14-07-02 | ECLASS 12.0 | 27-14-07-02 |

Approvals

Approvals



| | |
|-----------------------|------------|
| ROHS | Conform |
| UL File Number Search | UL Website |
| Certificate No. (UR) | E317499 |

Downloads

| | |
|---|--|
| Approval/Certificate/Document of Conformity | DE PI830000160627_002 |
| Engineering Data | WSCAD, EPLAN |
| Catalogues | Catalogues in PDF-format |

Datenblatt

CB 250/4,8 BK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

