

CB 540/7,5 NC**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



CB cable ties for the fastening of cables and markers.

- They are particularly suitable for fastening CLI M, SFX, WKM and WKS cable markers
- IEC 62275: 2006-conformant
- Fracture-resistant polyamide PA 6.6 with flammability rating V2 to UL-94

General ordering data

Version	Cable ties, 7.5 x 540 mm, Polyamide 66, 540 N
Order No.	7940006072
Type	CB 540/7,5 NC
GTIN (EAN)	4032248520312
Qty.	100 Stück

Erstellungs-Datum June 1, 2023 11:28:07 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

CB 540/7,5 NC

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	1.75 mm	Depth (inches)	0.069 inch
Height	540 mm	Height (inches)	21.26 inch
Width	7.5 mm	Width (inches)	0.295 inch
Net weight	6.9 g		

Temperatures

Operating temperature range	-40...85 °C	Operating temperature, min.	-40 °C
Operating temperature, max.	85 °C		

Installation materials

Bundle diameter, max.	158 mm	Bundle diameter, min.	35 mm
Cable diameter, max.	158 mm	For re-opening	No
Halogen	No	Material	Polyamide 66
Operating temperature range, max.	85 °C	Operating temperature range, min.	-40 °C
Tensile strength	540 N	Tensile strength (Pound-force)	121 lbf
UL 94 flammability rating	V-2	UV-resistant	No

Classifications

ETIM 6.0	EC000046	ETIM 7.0	EC000046
ETIM 8.0	EC000046	ECLASS 9.0	27-14-07-02
ECLASS 9.1	27-14-07-02	ECLASS 10.0	27-14-07-02
ECLASS 11.0	27-14-07-02	ECLASS 12.0	27-14-07-02

Approvals

Approvals



ROHS	Conform
UL File Number Search	UL Website
Certificate No. (UR)	E317499

Downloads

Approval/Certificate/Document of Conformity	DE PI830000160627_002
Engineering Data	WSCAD, EPLAN
Catalogues	Catalogues in PDF-format

Datenblatt

CB 540/7,5 NC

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

