

KLIPPON POK3 4M20AB CSS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com



General ordering data

Version	Housing with threaded hole, 75 x 160 x 56.5, Glass fibre-reinforced polyester, Drill holes side A: 4 x M20x1.5, Drill holes side B: 4 x M20x1.5
Order No.	8000004162
Type	KLIPPON POK3 4M20AB CSS
GTIN (EAN)	4032248986071
Qty.	1 Stück
Unassembled to fit rail	1928080000
Assembled to fit rail	8000004146
Reference product	1305830000

Erstellungs-Datum June 5, 2023 10:46:52 AM CEST

KLIPPON POK3 4M20AB CSS

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	56.5 mm	Depth (inches)	2.224 inch
Height	75 mm	Height (inches)	2.953 inch
Width	160 mm	Width (inches)	6.299 inch
Net weight	428 g		

Certificate numbers enclosure

Certificate No. (EAC)	RUC-DE.BE02.B.00173
-----------------------	---------------------

Housing

Drill holes side A	4 x M20x1.5	Drill holes side B	4 x M20x1.5
Drill holes side C	none	Drill holes side D	none
Material	Glass fibre-reinforced polyester		

Classifications

ETIM 6.0	EC000261	ETIM 7.0	EC000261
ETIM 8.0	EC000261	ECLASS 9.0	27-18-01-01
ECLASS 9.1	27-18-92-90	ECLASS 10.0	27-18-01-01
ECLASS 11.0	27-18-01-01	ECLASS 12.0	27-18-01-01

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	c0b142f1-4049-4b95-bbc3-9959a2d3b09c

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
Brochures	

KLIPPON POK3 4M20AB CSS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

