

FPL 8G1.5/Q8KG/2**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

General ordering data

Version	FieldPower®, Cable, Plastic housing, Number of wires: 8, Ölflex Classic 110 8G1.5 or similar, Cross-section: 1.5 mm ² , 2 m
Order No.	8000005238
Type	FPL 8G1.5/Q8KG/2
GTIN (EAN)	4032248997701
Qty.	1 Stück

Erstellungs-Datum June 5, 2023 10:47:32 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

FPL 8G1.5/Q8KG/2

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 498 g

Technical specifications for cable

Bending radius, min., moving	159 mm	Bending radius, min., stationary	42,4 mm
Number of wires	8		

General technical data

Protection degree IP65

Classifications

ETIM 6.0	EC001578	ETIM 7.0	EC003250
ETIM 8.0	EC003250	ECLASS 9.0	27-06-20-11
ECLASS 9.1	27-06-90-90	ECLASS 10.0	27-06-01-06
ECLASS 11.0	27-06-01-06	ECLASS 12.0	27-06-01-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	edb4769d-47d5-4f66-921a-c1f4685d793c

Approvals

Approvals



ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)

FPL 8G1.5/Q8KG/2

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Zeichnungen

