

FPL 4G2.5/P/Q4MG/2**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

General ordering data

Version	FieldPower®, Cable, Metal housing, Number of wires: 4, Ölflex Classic 110 4G2.5 or similar, Cross-section: 2.5 mm ² , 2 m
Order No.	8000005294
Type	FPL 4G2.5/P/Q4MG/2
GTIN (EAN)	4032248997602
Qty.	1 Stück

FPL 4G2.5/P/Q4MG/2

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 665 g

Technical specifications for cable

Bending radius, min., moving	133.5 mm	Bending radius, min., stationary	35,6 mm
Halogen	Yes	Number of wires	4
Temperature range, moving	-5...70 °C	Temperature range, stationary	-40...70 °C

General technical data

Protection degree IP65

Classifications

ETIM 6.0	EC001576	ETIM 7.0	EC001576
ETIM 8.0	EC001576	ECLASS 9.0	27-06-04-02
ECLASS 9.1	27-06-91-90	ECLASS 10.0	27-06-04-02
ECLASS 11.0	27-06-04-02	ECLASS 12.0	27-06-04-02

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3
SCIP	1aeccc23-6820-414b-bb61-68f12b86e9f3

Approvals

Approvals



ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)

FPL 4G2.5/P/Q4MG/2

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

Zeichnungen

