

**FPL 4G2.5/Q8KW/3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

**General ordering data**

Version	FieldPower®, Cable, Plastic housing, Number of wires: 4, Ölflex Classic 110 4G2.5 or similar, Cross-section: 2.5 mm <sup>2</sup> , 3 m
Order No.	<a href="#">8000011742</a>
Type	FPL 4G2.5/Q8KW/3
GTIN (EAN)	4050118190403
Qty.	1 Stück

Erstellungs-Datum June 5, 2023 10:48:24 AM CEST

Katalogstand 26.05.2023 / Technische Änderungen vorbehalten

## FPL 4G2.5/Q8KW/3

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Dimensions and weights

Net weight 550 g

### Technical specifications for cable

Number of wires 4

### General technical data

Protection degree	IP65	Rated current	16 A
Rated voltage	500 V		

### Classifications

ETIM 6.0	EC001578	ETIM 7.0	EC003250
ETIM 8.0	EC003250	ECLASS 9.0	27-06-20-11
ECLASS 9.1	27-06-90-90	ECLASS 10.0	27-06-01-06
ECLASS 11.0	27-06-01-06	ECLASS 12.0	27-06-01-06

### Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	edb4769d-47d5-4f66-921a-c1f4685d793c

### Approvals

Approvals



ROHS Conform

### Downloads

Catalogues [Catalogues in PDF-format](#)

## FPL 4G2.5/Q8KW/3

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

## Zeichnungen

[www.weidmueller.com](http://www.weidmueller.com)

### Pin assignments

	Pin	Conductor	Assignment
8 = nc	1	1	U
	2	-	-
5 = nc	3	3	W
	4	-	-
PE	5	-	-
	6	-	-
3 = W	7	2	V
	8	-	-
2 = nc	PE	gr./yell.	PE