

FPL 4G2.5/Q8KW/5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Take advantage of our pre-assembled FieldPower® connectors with HQ connectors acc. to IEC 23570 (DESINA) for connecting decentralised motor controller devices quickly and conveniently.

General ordering data

Order No.	8000011743
Type	FPL 4G2.5/Q8KW/5
GTIN (EAN)	4050118190410
Qty.	1 Stück

FPL 4G2.5/Q8KW/5

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Net weight 893 g

Technical specifications for cable

Number of wires 4

General technical data

Protection degree	IP65	Rated current	16 A
Rated voltage	500 V		

Classifications

ETIM 6.0	EC001578	ETIM 7.0	EC003250
ETIM 8.0	EC003250	ECLASS 9.0	27-06-20-11
ECLASS 9.1	27-06-90-90	ECLASS 10.0	27-06-01-06
ECLASS 11.0	27-06-01-06	ECLASS 12.0	27-06-01-06

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1 Potassium perfluorobutane sulfonate 29420-49-3 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1
SCIP	edb4769d-47d5-4f66-921a-c1f4685d793c

Approvals

Approvals



ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)

FPL 4G2.5/Q8KW/5

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

Zeichnungen

www.weidmueller.com

Pin assignments

	Pin	Conductor	Assignment
8 = nc	1	1	U
	2	-	-
5 = nc	3	3	W
	4	-	-
PE	5	-	-
	6	-	-
3 = W	7	2	V
	8	-	-
2 = nc	PE	gr./yell.	PE