

TS35X7.5 ST FPC 40 VER**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Similar to illustration

Similar to illustration

Accessories

General ordering data

| | |
|------------|---|
| Version | Rail, TS 35, TS 35 x 7.5, Width: 365 mm, Steel, galvanized, chromium-plated |
| Order No. | 8000037562 |
| Type | TS35X7.5 ST FPC 40 VER |
| GTIN (EAN) | 4050118653267 |
| Qty. | 20 Stück |

Erstellungs-Datum May 26, 2023 3:33:23 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

TS35X7.5 ST FPC 40 VER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

| | | | |
|------------|-----------|-----------------|------------|
| Depth | 7.5 mm | Depth (inches) | 0.295 inch |
| Height | 35 mm | Height (inches) | 1.378 inch |
| Width | 365 mm | Width (inches) | 14.37 inch |
| Net weight | 125.375 g | | |

General information

| | | | |
|---------------------|-----------------|--------------------|-----------------------------|
| Installation advice | Direct mounting | Integral fixing | Screwed |
| Material | Steel | Material thickness | 1 mm |
| Standards | DIN EN 60715 | Surface finish | galvanized, chromium-plated |

Classifications

| | | | |
|-------------|-------------|-------------|-------------|
| ETIM 6.0 | EC001285 | ETIM 7.0 | EC001285 |
| ETIM 8.0 | EC001285 | ECLASS 9.0 | 27-40-06-02 |
| ECLASS 9.1 | 27-40-06-02 | ECLASS 10.0 | 27-40-06-02 |
| ECLASS 11.0 | 27-40-06-02 | ECLASS 12.0 | 27-40-06-02 |

Downloads

| | |
|------------------|--|
| Engineering Data | CAD data – STEP |
| Catalogues | Catalogues in PDF-format |