

**TS15X5 ST MPC1217 VER**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

[www.weidmueller.com](http://www.weidmueller.com)

**Similar to illustration**

Similar to illustration

Accessories

**General ordering data**

Version	Rail, TS 15, Width: 60 mm, without slot, Steel, galvanized, chromium-plated
Order No.	<a href="#">8000037598</a>
Type	TS15X5 ST MPC1217 VER
GTIN (EAN)	4050118653106
Qty.	20 Stück

Erstellungs-Datum May 26, 2023 3:33:57 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## TS15X5 ST MPC1217 VER

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	5 mm	Depth (inches)	0.197 inch
Height	15 mm	Height (inches)	0.591 inch
Width	60 mm	Width (inches)	2.362 inch
Net weight	18.278 g		

### General information

Installation advice	Direct mounting	Integral fixing	Screwed
Material	Steel	Material thickness	1 mm
Standards	DIN EN 60715	Surface finish	galvanized, chromium-plated

### Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>