

TS15X5 ST FPC 20 VER

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Similar to illustration

Similar to illustration

Accessories

General ordering data

Version	Rail, TS 15, Width: 235 mm, without slot, Steel, galvanized, chromium-plated
Order No.	8000037604
Type	TS15X5 ST FPC 20 VER
GTIN (EAN)	4050118653168
Qty.	20 Stück

Erstellungs-Datum May 26, 2023 3:36:12 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

TS15X5 ST FPC 20 VER

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 26
 D-32758 Detmold
 Germany

www.weidmueller.com

Technische Daten

Dimensions and weights

Depth	5 mm	Depth (inches)	0.197 inch
Height	15 mm	Height (inches)	0.591 inch
Width	235 mm	Width (inches)	9.252 inch
Net weight	29.95 g		

General information

Installation advice	Direct mounting	Integral fixing	Screwed
Material	Steel	Material thickness	1 mm
Standards	DIN EN 60715	Surface finish	galvanized, chromium-plated

Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02

Downloads

Engineering Data	CAD data – STEP
Catalogues	Catalogues in PDF-format