

**TS35 MPC 1725 VER****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

[www.weidmueller.com](http://www.weidmueller.com)**Similar to illustration**

Similar to illustration

Accessories

**General ordering data**

Version	Rail, TS 35 x 7.5, TS 35, Width: 98 mm, without slot, Steel, galvanized, chromium-plated
Order No.	<a href="#">8000037607</a>
Type	TS35 MPC 1725 VER
GTIN (EAN)	4050118653199
Qty.	20 Stück

Erstellungs-Datum May 26, 2023 3:39:19 PM CEST

Katalogstand 12.05.2023 / Technische Änderungen vorbehalten

## TS35 MPC 1725 VER

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 26  
 D-32758 Detmold  
 Germany

www.weidmueller.com

## Technische Daten

### Dimensions and weights

Depth	7.5 mm	Depth (inches)	0.295 inch
Height	35 mm	Height (inches)	1.378 inch
Width	98 mm	Width (inches)	3.858 inch
Net weight	20.489 g		

### General information

Installation advice	Direct mounting	Integral fixing	Screwed
Material	Steel	Standards	DIN EN 60715
Surface finish	galvanized, chromium-plated		

### Classifications

ETIM 6.0	EC001285	ETIM 7.0	EC001285
ETIM 8.0	EC001285	ECLASS 9.0	27-40-06-02
ECLASS 9.1	27-40-06-02	ECLASS 10.0	27-40-06-02
ECLASS 11.0	27-40-06-02	ECLASS 12.0	27-40-06-02

### Downloads

Catalogues [Catalogues in PDF-format](#)