

FBK 40/300 RK**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The pre-assembled control cables have pluggable 10- or 40-pole socket blocks according to IEC 603/1 DIN 41 651. They can be used to connect the PLC front adapter to the active or passive Weidmüller interfaces. They are available in different lengths.

General ordering data

Version	Pre-assembled cable, FBK, FLAT CABLE PLANO HE10 40P
Order No.	8216390000
Type	FBK 40/300 RK
GTIN (EAN)	4008 190264697
Qty.	1 pc(s).

Creation date March 20, 2023 11:16:00 AM CET

Catalogue status 17.03.2023 / We reserve the right to make technical changes.

FBK 40/300 RK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	503 g
------------	-------

Temperatures

Storage temperature	-10...70 °C
---------------------	-------------

General Data

Cable	Cable LiYY	Cable length	3 m
Connector PLC side	FLAT CABLE PLANO HE10 40P	Interface connector	FLAT CABLE PLANO HE10 40P
Material	PVC	Number of poles, min.	40-pole
Suitable for	Digital signals	Wire cross-section	0.14 mm ²

Electrical Data

Permissible current strength per path, max.	1 A	Rated voltage	< 50 V AC, ≤ 50 V DC
Resistance	55 mΩ/m	Total current, max.	3 A

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20	ECLASS 12.0	27-24-22-20

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Catalogues	Catalogues in PDF-format
------------	--