

FBK 10/100 RK

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



Similar to illustration

The pre-assembled control cables have pluggable 10- or 40-pole socket blocks according to IEC 603/1 DIN 41 651. They can be used to connect the PLC front adapter to the active or passive Weidmüller interfaces. They are available in different lengths.

General ordering data

Version	Pre-assembled cable, FBK, FLAT CABLE CONNECTOR HE10 10P
Order No.	8235360000
Type	FBK 10/100 RK
GTIN (EAN)	4008 190264581
Qty.	1 pc(s).

Creation date March 20, 2023 11:16:36 AM CET

Catalogue status 17.03.2023 / We reserve the right to make technical changes.

FBK 10/100 RK

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Dimensions and weights

Net weight 68 g

Temperatures

Storage temperature -10...70 °C

General Data

Cable	Cable LiYY	Cable length	1 m
Connector PLC side	FLAT CABLE CONECTOR HE10 10P	Interface connector	FLAT CABLE CONECTOR HE10 10P
Material	PVC	Number of poles, min.	10-pole
Suitable for	Digital signals	Wire cross-section	0.14 mm ²

Electrical Data

Permissible current strength per path, max.	1 A	Rated voltage	< 50 V AC, ≤ 50 V DC
Resistance	55 mΩ/m	Total current, max.	3 A

Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20	ECLASS 12.0	27-24-22-20

Approvals

Approvals



ROHS Conform

Downloads

Catalogues [Catalogues in PDF-format](#)