

**FBK 10/400 RK****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



Similar to illustration

The pre-assembled control cables have pluggable 10- or 40-pole socket blocks according to IEC 603/1 DIN 41 651. They can be used to connect the PLC front adapter to the active or passive Weidmüller interfaces. They are available in different lengths.

**General ordering data**

Version	Pre-assembled cable, FBK, FLAT CABLE CONNECTOR HE10 10P
Order No.	<a href="#">8235420000</a>
Type	FBK 10/400 RK
GTIN (EAN)	4008 190264642
Qty.	1 pc(s).

Creation date March 20, 2023 11:17:03 AM CET

Catalogue status 17.03.2023 / We reserve the right to make technical changes.

## FBK 10/400 RK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

Net weight	253 g
------------	-------

## Temperatures

Storage temperature	-10...70 °C
---------------------	-------------

## General Data

Cable	Cable LiYY	Cable length	4 m
Connector PLC side	FLAT CABLE CONECTOR HE10 10P	Interface connector	FLAT CABLE CONECTOR HE10 10P
Material	PVC	Number of poles, min.	10-pole
Suitable for	Digital signals	Wire cross-section	0.14 mm <sup>2</sup>

## Electrical Data

Permissible current strength per path, max.	1 A	Rated voltage	< 50 V AC, ≤ 50 V DC
Resistance	55 mΩ/m	Total current, max.	3 A

## Classifications

ETIM 6.0	EC000237	ETIM 7.0	EC000237
ETIM 8.0	EC000237	ECLASS 9.0	27-24-22-20
ECLASS 9.1	27-24-22-20	ECLASS 10.0	27-24-22-20
ECLASS 11.0	27-24-22-20	ECLASS 12.0	27-24-22-20

## Approvals

Approvals



ROHS	Conform
------	---------

## Downloads

Catalogues	<a href="#">Catalogues in PDF-format</a>
------------	--