

IE-CT

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



The fully insulated plastic housings of our continuity testers are shockproof and unbreakable, making these instruments ideal for daily use, even in tough conditions. The integrated torch makes it easier to locate defective cables quickly and safely. The results of the continuity test can be conveyed visually and acoustically.

General ordering data

Version	Continuity tester for data cables
Order No.	8808420000
Type	IE-CT
GTIN (EAN)	4032248506002
Qty.	1 Stück

IE-CT

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Height	36 mm	Height (inches)	1.417 inch
Width	70 mm	Width (inches)	2.756 inch
Length	140 mm	Length (inches)	5.512 inch
Net weight	396 g		

Measuring and testing devices

Display	digital	Supply	9V battery
---------	---------	--------	------------

Classifications

ETIM 6.0	EC002080	ETIM 7.0	EC002080
ETIM 8.0	EC002080	ECLASS 9.0	27-20-11-08
ECLASS 9.1	27-20-03-90	ECLASS 10.0	27-20-11-08
ECLASS 11.0	27-20-11-08	ECLASS 12.0	27-20-11-08

Approvals

Approvals



ROHS Conform

Downloads

User Documentation	Manual MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN FL FIELDWIRING EN PI PROFINET CABLING EN