

**IE-FM6Z2VO0002MST0SD0X****Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Assembled IE cables, FO patch cable, multimode, SC duplex - ST, orange, Core diameter 62.5 µm

**General ordering data**

Version	Pre-assembled patch cable, crossover, SC duplex IP 20, ST IP 20, 62.5 µm, PVC, 2 m
Order No.	<a href="#">881340000</a>
Type	IE-FM6Z2VO0002MST0SD0X
GTIN (EAN)	4032248513253
Qty.	1 Stück

**IE-FM6Z2VO0002MST0SD0X**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

**Technische Daten**

**Dimensions and weights**

Length	2 m	Length (inches)	78.74 inch
Net weight	54.4 g		

**Temperatures**

Storage temperature	-25 °C...75 °C	Operating temperature	-5 °C...75 °C
Operating temperature, min.	-5 °C	Operating temperature, max.	75 °C
Installation temperature	-5 °C...50 °C		

**General standards**

Connector standard	IEC 61754-2, IEC 61754-4
--------------------	--------------------------

**Standards**

Connector standard	IEC 61754-2, IEC 61754-4
--------------------	--------------------------

**Cable structure**

Cable layout	ZIPCORD	Core diameter	62.5 µm
Material sheath	PVC	Primary coating	245 µm
Sheath diameter	3*6 mm	Sheathing colour	orange
Standard designations	I-V(ZN)Y		

**Mechanical and material properties of cable**

Min. bending radius, once only	30 mm	Min. bending radius, repetitive	60 mm
--------------------------------	-------	---------------------------------	-------

**Plug**

Plug	Cable side	left
	Version of contact face	SC-Duplex
	Protection degree (IP)	IP20
	Gender of contact	male contact
	Outlet direction	straight
	Version of connector	plug
	Housing main material	Plastic
	Status indicator available	No
	Shielding available	No
	Cable side	right
	Version of contact face	ST
	Protection degree (IP)	IP20
	Gender of contact	male contact
	Outlet direction	straight
	Version of connector	plug
	Housing main material	Plastic
Status indicator available	No	
Shielding available	No	
Plug left	SC-Duplex, IP20, male contact, straight, plug, Plastic, unshielded	
Plug right	ST, IP20, male contact, straight, plug, Plastic, unshielded	

**IE-FM6Z2VO0002MST0SD0X**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com) SC Duplex, IP20, male contact, straight, plug, Plastic, unshielded

**Technische Daten**

**Plug, left**

Connector left	Plug left	SC duplex IP 20	SC Duplex, IP20, male contact, straight, plug, Plastic, unshielded
----------------	-----------	-----------------	--

**Plug, right**

Connector right	Plug right	ST IP 20	ST, IP20, male contact, straight, plug, Plastic, unshielded
-----------------	------------	----------	---

**Classifications**

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ECLASS 9.0	27-06-10-03
ECLASS 9.1	27-06-10-03	ECLASS 10.0	27-06-10-03
ECLASS 11.0	27-06-10-03	ECLASS 12.0	27-06-10-03

**Environmental Product Compliance**

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

**Approvals**

ROHS	Conform
------	---------

**Downloads**

User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>

**IE-FM6Z2V00002MST0SD0X**

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

**Zeichnungen**

**Detailed drawing**

