

## IE-DPC

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



For protecting your devices against dust and dirt.

### General ordering data

Version	Flange-mounted housing, protective cap
Order No.	<a href="#">8813490000</a>
Type	IE-DPC
GTIN (EAN)	40322485 13338
Qty.	100 Stück

## IE-DPC

**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

[info@weidmueller.com](mailto:info@weidmueller.com)

[www.weidmueller.com](http://www.weidmueller.com)

## Technische Daten

### Dimensions and weights

Depth	17.2 mm	Depth (inches)	0.677 inch
Net weight	1.1 g		

### Temperatures

Operating temperature	-50 °C...85 °C	Operating temperature, min.	-50 °C
Operating temperature, max.	85 °C		

### General data

Colour	black	Housing main material	TPR
Type of mounting	Indoors only	UL 94 flammability rating	HB

### Classifications

ETIM 6.0	EC002314	ETIM 7.0	EC002314
ETIM 8.0	EC002314	ECLASS 9.0	27-44-02-08
ECLASS 9.1	27-44-02-08	ECLASS 10.0	27-44-02-08
ECLASS 11.0	27-44-02-08	ECLASS 12.0	27-44-02-08

### Approvals

ROHS	Conform
------	---------

### Downloads

Engineering Data	<a href="#">CAD data – STEP</a>
User Documentation	<a href="#">MAN IE GUIDE DE</a> <a href="#">MAN IE GUIDE EN</a>
Catalogues	<a href="#">Catalogues in PDF-format</a>
Brochures	<a href="#">FL FIELDWIRING EN</a> <a href="#">PI PROFINET CABLING EN</a> <a href="#">PI PROFINET CABLING EN</a>