

SCM-I CLIP P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Product image



Retaining clip for RIDERSERIES RCM relays
• Metal and plastic retaining clip

General ordering data

Version	RIDERSERIES RCM, Retaining clip
Order No.	8869440000
Type	SCM-I CLIP P
GTIN (EAN)	40322486 14295
Qty.	10 pc(s).

Creation date February 16, 2023 12:40:24 PM CET

Catalogue status 03.02.2023 / We reserve the right to make technical changes.

SCM-I CLIP P**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	54.2 mm	Depth (inches)	2.134 inch
Height	37.8 mm	Height (inches)	1.488 inch
Width	27 mm	Width (inches)	1.063 inch
Net weight	4.744 g		

Temperatures

Storage temperature	-40 °C...85 °C	Operating temperature	-40 °C...70 °C
Operating temperature, min.	-40 °C	Operating temperature, max.	70 °C
Humidity	40 °C / 93 % rel. humidity, no condensation		

General data

Material	Plastic	Colour	orange
----------	---------	--------	--------

Classifications

ETIM 6.0	EC002586	ETIM 7.0	EC002586
ETIM 8.0	EC002586	ECLASS 9.1	27-37-16-92
ECLASS 10.0	27-37-16-92	ECLASS 11.0	27-37-16-92
ECLASS 12.0	27-37-16-92		

Approvals

Approvals



ROHS Conform

Downloads

Engineering Data	CAD data – STEP
Engineering Data	WSCAD
Catalogues	Catalogues in PDF-format
Brochures	

Data sheet

SCM-I CLIP P

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensional drawing

