

**SCM-I MARK**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 26  
D-32758 Detmold  
Germany

www.weidmueller.com

**Product image**



**General ordering data**

|            |                            |
|------------|----------------------------|
| Version    | RIDERSERIES RCM, Label     |
| Order No.  | <a href="#">8869460000</a> |
| Type       | SCM-I MARK                 |
| GTIN (EAN) | 40322486 14417             |
| Qty.       | 10 pc(s).                  |

## SCM-I MARK

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

## Technical data

## Dimensions and weights

|            |         |                 |            |
|------------|---------|-----------------|------------|
| Depth      | 8.5 mm  | Depth (inches)  | 0.335 inch |
| Height     | 8 mm    | Height (inches) | 0.315 inch |
| Width      | 26.5 mm | Width (inches)  | 1.043 inch |
| Net weight | 0.7 g   |                 |            |

## Temperatures

|                             |  |                             |                |
|-----------------------------|--|-----------------------------|----------------|
| Storage temperature         | -40 °C...85 °C                                 | Operating temperature       | -40 °C...70 °C |
| Operating temperature, min. | -40 °C   | Operating temperature, max. | 70 °C          |
| Humidity                    | 40 °C / 93 % rel. humidity,<br>no condensation |                             |                |

## General data

|                           |  |        |       |
|---------------------------|--|--------|-------|
| Printing                  | Individual markers / Not<br>for use with PRINT JET | Colour | white |
| UL 94 flammability rating | V-0  |        |       |

## Classifications

|             |             |             |             |
|-------------|-------------|-------------|-------------|
| ETIM 6.0    | EC001288    | ETIM 7.0    | EC001288    |
| ETIM 8.0    | EC001288    | ECLASS 9.0  | 27-40-06-29 |
| ECLASS 9.1  | 27-40-06-29 | ECLASS 10.0 | 27-40-06-29 |
| ECLASS 11.0 | 27-28-11-04 | ECLASS 12.0 | 27-28-11-04 |

## Approvals

Approvals



ROHS

Conform

## Downloads

|                  |  |
|------------------|--|
| Engineering Data | <a href="#">CAD data – STEP</a>          |
| Engineering Data | <a href="#">WSCAD</a>                    |
| Catalogues       | <a href="#">Catalogues in PDF-format</a> |
| Brochures        |  |