

IE-FM5Z2VO0005MST0ST0X**Weidmüller Interfaces GmbH & Co. KG**

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com



Assembled IE cables, FO patch cable, multimode, ST-ST,
orange, Core diameter 50 µm

General ordering data

Version	Patch cable, ST IP 20, ST IP 20, 50 µm, PVC, 5 m
Order No.	8876370050
Type	IE-FM5Z2VO0005MST0ST0X
GTIN (EAN)	4032248609741
Qty.	1 Stück

IE-FM5Z2V00005MST0ST0X

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Technische Daten

Dimensions and weights

Length	5 m	Length (inches)	196.85 inch
Net weight	80 g		

Temperatures

Storage temperature	-25 °C...75 °C	Operating temperature	-5 °C...75 °C
Operating temperature, min.	-5 °C	Operating temperature, max.	75 °C
Installation temperature	-5 °C...50 °C		

General standards

Connector standard	IEC 61754-2
--------------------	-------------

Standards

Connector standard	IEC 61754-2
--------------------	-------------

Cable structure

Cable layout	ZIPCORD	Core diameter	50 µm
Material sheath	PVC	Primary coating	245 µm
Sheath diameter	3*6 mm	Sheathing colour	orange
Standard designations	I-V(ZN)Y		

Mechanical and material properties of cable

Min. bending radius, once only	30 mm	Min. bending radius, repetitive	60 mm
--------------------------------	-------	---------------------------------	-------

Plug

Plug	Cable side	left	
	Version of contact face	ST	
	Protection degree (IP)	IP20	
	Gender of contact	male contact	
	Outlet direction	straight	
	Version of connector	plug	
	Housing main material	Plastic	
	Status indicator available	No	
	Shielding available	No	
	Cable side	right	
	Version of contact face	ST	
	Protection degree (IP)	IP20	
	Gender of contact	male contact	
	Outlet direction	straight	
	Version of connector	plug	
	Housing main material	Plastic	
	Status indicator available	No	
	Shielding available	No	
	Plug left	ST, IP20, male contact, straight, plug, Plastic, unshielded	
	Plug right	ST, IP20, male contact, straight, plug, Plastic, unshielded	

IE-FM5Z2V00005MST0ST0X

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com ST, IP20, male contact, straight, plug, Plastic, unshielded

Technische Daten

Plug, left

Connector left	Plug left	ST IP 20	ST, IP20, male contact, straight, plug, Plastic, unshielded
----------------	-----------	----------	---

Plug, right

Connector right	Plug right	ST IP 20	ST, IP20, male contact, straight, plug, Plastic, unshielded
-----------------	------------	----------	---

Classifications

ETIM 6.0	EC002607	ETIM 7.0	EC002607
ETIM 8.0	EC002607	ECLASS 9.0	27-06-10-03
ECLASS 9.1	27-06-10-03	ECLASS 10.0	27-06-10-03
ECLASS 11.0	27-06-10-03	ECLASS 12.0	27-06-10-03

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
SCIP	67cf1078-beca-4687-860b-dc475a6ec24a

Approvals

ROHS	Conform
------	---------

Downloads

User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN
Catalogues	Catalogues in PDF-format
Brochures	FL FIELDWIRING EN PI PROFINET CABLING EN PI PROFINET CABLING EN

IE-FM5Z2V00005MST0ST0X

Weidmüller Interfaces GmbH & Co. KG

Postfach 3030

32760 Detmold

Tel. +49 5231 14-0

Fax. +49 5231 14-2083

info@weidmueller.com

www.weidmueller.com

Zeichnungen

Detailed drawing

